

# Infrared-to-Visible Converters

## IR Laser Beam Visualizers / IR Detectors

### IR-VIS Series



#### Applications

- Detection & Visualization of IR Radiation from CW Lasers, Pulsed Lasers, and IR Laser Diodes
- Identification of Mode Structure

#### Features

- High Sensitivity
- High Damage Threshold
- Cover Wide Spectral Ranges
- No Activation Needed
- No Bleaching

The IR-VIS series from ALPHALAS are unique infrared-to-visible converters suitable for CW and pulsed IR laser sources as well as IR laser diodes. They are ideally suited for tasks like detecting invisible IR radiation, identifying mode structure, etc. Therefore, the visualizers are indispensable tools for every laboratory using Nd:YAG or other IR lasers.

Based on a special durable ceramic-like material, the detectors combine high sensitivity with high damage threshold. In contrast to other conventional infrared-to-visible converters, the IR-VIS series from ALPHALAS

do not need any activation with daylight or UV light and can therefore be used in darkened rooms. In addition, the irradiated area does not bleach. If the surface of the active area has been damaged, the upper layer can be simply removed using a fine file or sand paper. The new fresh surface is as good as the original one.

The standard -S and -D models cover two IR spectral ranges from 800 nm to 1100 nm and from 1460 nm to 1600 nm, resulting in green and orange emission correspondingly. The diameter of the active area is 15 mm or 40 mm.

The -S models are single-sided and the -D model is double-sided.

The special -QM model is for Q-switched and modelocked lasers only. It is based on an efficient second-harmonic generation process and covers the wide spectral range from 800 nm to 1400 nm. It is also double-sided and has a diameter of 30 mm.

#### IR-VIS Series • Available Models

Model	IR Wavelength Ranges (nm)	Emission	Sensitivity	Damage Threshold	Dynamic Range	Suitable for Type of Lasers	Active Area (mm)
IR-VIS-40-S	800 - 1100 and 1460 - 1600	green and orange	CW: 40 mW/cm <sup>2</sup> Pulsed: 0.1 mJ/cm <sup>2</sup>	CW: 300 W/cm <sup>2</sup> Pulsed: 1 J/cm <sup>2</sup>	> 100:1	CW, pulsed	Ø 40
IR-VIS-40-D	800 - 1100 and 1460 - 1600	green and orange	CW: 40 mW/cm <sup>2</sup> Pulsed: 0.1 mJ/cm <sup>2</sup>	CW: 300 W/cm <sup>2</sup> Pulsed: 1 J/cm <sup>2</sup>	> 100:1	CW, pulsed	Ø 40 double-sided
IR-VIS-15-S	800 - 1100 and 1460 - 1600	green and orange	CW: 40 mW/cm <sup>2</sup> Pulsed: 0.1 mJ/cm <sup>2</sup>	CW: 300 W/cm <sup>2</sup> Pulsed: 1 J/cm <sup>2</sup>	> 100:1	CW, pulsed	Ø 15
IR-VIS-30-QM	800 - 1400	second harmonic	Pulsed only: min. 100 kW/cm <sup>2</sup>	QCW: 1 W/cm <sup>2</sup> Pulsed: 1 mJ/cm <sup>2</sup>	> 1000:1	pulsed, low-average, high peak power	Ø 30 double-sided

**Note:** All models are in anodized holders.

**Always use laser safety eyewear when working with the IR-VIS detectors.**

ALPHALAS GMBH  
Bertha-von-Suttner-Str. 5  
D-37085 Goettingen  
Germany

TEL +49 - 551 - 77 06 147  
FAX +49 - 551 - 77 06 146  
E-MAIL sales@alphalas.com  
WEB www.alphalas.com

LASERS, OPTICS, ELECTRONICS.  
MADE IN GERMANY.  
WWW.ALPHALAS.COM



Options and further specifications are available upon request. Specifications in this data sheet are subject to change without notice. No responsibility for typing or printing errors. ALPHALAS GmbH reserves the right to make changes without further notice to any products herein. ALPHALAS GmbH makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ALPHALAS GmbH assume any liability arising out of the application or use of any product, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in ALPHALAS GmbH data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. ALPHALAS GmbH products are intended for expert users only. ALPHALAS GmbH products are not designed, intended, or authorized for use in medical, surgical or any other human *in vivo* applications, or for any other application in which the failure of the ALPHALAS GmbH product could create a situation where personal injury or death may occur. Therefore, ALPHALAS GmbH products must not be used in such applications. Furthermore, ALPHALAS GmbH products must not be used in critical applications (e.g. in life support systems, in aviation, in nuclear facilities, in weapon systems, in safety or security systems, etc.). ALPHALAS GmbH products must not be used where damage to property may occur.