

EPIGAP Optronik GmbH

Koepenicker Str. 325b
 D-12555 Berlin
 Fon: +49 (0)30 657637 60
 Fax: +49 (0)30 657637 70
 sales@epigap-optronic.de



Data Sheet

page 1 of 2

UV photodiode

EOPD-280-0-0.3-2-1

Rev. 02, 2015

| Radiation | Type | Technology | Case |
|-------------|----------|------------|-------|
| ultraviolet | UV-glass | SiC | TO-39 |

| Description: | |
|--------------------------------|---|
| <p>1: Cathode 2: Anode</p> | <p>Highly reliable photodiode with high spectral sensitivity in the UV range (210 nm - 380 nm), mounted in hermetically sealed TO-39 package with UV-glass window</p> |

Maximum Ratings

$T_{amb} = 25^{\circ}\text{C}$, unless otherwise specified

| Parameter | Symbol | Value | Unit |
|-----------------------------|-----------|-------------|-----------------|
| Active area | A | 0.055 | mm ² |
| Operating temperature range | T_{amb} | -25 to +70 | °C |
| Storage temperature range | T_{stg} | -40 to +100 | °C |

Optical and Electrical Characteristics

$T_{amb} = 25^{\circ}\text{C}$, unless otherwise specified

| Parameter | Test conditions | Symbol | Min | Typ | Max | Unit |
|---------------------------------|-------------------------|--------------------------------|-----|------|-----|------|
| Breakdown voltage ¹⁾ | $I_R = 100 \mu\text{A}$ | V_R | | 20 | | V |
| Dark current | $V_R = 1 \text{ V}$ | I_D | | 1 | | fA |
| Peak sensitivity wavelength | $V_R = 0 \text{ V}$ | λ_p | | 275 | | nm |
| Responsivity at λ_p | $V_R = 0 \text{ V}$ | S_λ | | 0.13 | | A/W |
| Sensitivity range at 1% | $V_R = 0 \text{ V}$ | $\lambda_{min}, \lambda_{max}$ | 210 | | 380 | nm |
| Junction capacitance | $V_R = 0 \text{ V}$ | C_J | | 21 | | pF |

¹⁾ for information only



We reserve the right to make changes to improve technical design and may do so without further notice. Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer.

EPIGAP Optronik GmbH

Koepenicker Str. 325b
D-12555 Berlin
Fon: +49 (0)30 657637 60
Fax: +49 (0)30 657637 70
sales@epigap-optronic.de




Data Sheet

page 2 of 2

UV photodiode

EOPD-280-0-0.3-2-1

Rev. 02, 2015



We reserve the right to make changes to improve technical design and may do so without further notice. Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer.